



## WA141206GIE

by Wiegmann  
Catalog ID: WA141206GIE

N12 JIC Hinged Screw-Cover 14X12X6 Carbon Steel - Gray

Designed for use as instrument housing, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil, and water.

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes.
- Lids are sealed with closed cell oil resistant neoprene gasket. Cover is secured by continuous hinge. Captivated door screws thread into sealed wells. No mounting feet or mounting holes are provided. Weldnuts are provided to mount optional panels. Grounding provisions provided.

## Product Details

### General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection from dirt, dust, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Hinged Screw Cover
Finish Type	Textured
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725442607

### Dimensions

Depth	6 in
Height	14 in
Weight	15 lb
Width	12 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes