



## WA202008GSCG

by Wiegmann  
Catalog ID: WA202008GSCG

N4 Gasketed Screw-Cover 20X20X8 Carbon Steel - Galvanized

- Bodies and covers fabricated from 14 gauge G-90 grade galvanized steel. Seams are continuously welded and ground smooth. Cover contains closed cell oil resistant neoprene gasket. Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc from entering into the box through the screw holes. Ground stud located in door. No holes, knockout, or rear mounting holes.

## Product Details

### General

Application	Designed for use as wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Galvanized
Listings	UL
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725848843

### Dimensions

Actual Depth	11.25 in
Actual Height	11.250 in
Actual Width	20.060 in
Cubic Capacity	2420 cu.in
Depth	11 in
Height	11 in
Weight	46 lb
Width	20 in

## Certifications and Compliance

Certified Listed	UL
Nema Rating	4
UL Listed	Yes