



WA4AXFN

by Wiegmann
Catalog ID: WA4AXFN

AXIAL FAN - 115V / 100CFM 4 IN.

- Fan furnished standard with 24 inch lead wire, 90 degree plug attached
- Impeller and frame are glass reinforced thermoplastic, UL94-V0
- Rated Speed (RPM) 2500/3000
- Noise Level 37 +/- 2
- Maximum Air Flow (M3/MIN) 2.5/3.1
- Maximum Air Flow (CFM) 88/110
- Maximum Static Pressure/H₂O 5.8/7