



WA60X4912U

by Wiegmann
Catalog ID: WA60X4912U

N12 Two Door Floor-Mount Right Flanged Disconnect 60X49X12 Carbon Steel - Gray

Product Details

General

Application	The Wiegmann universal cutout is used in large freestand and floorstand enclosures.
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	15 in. floor stands
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725428502

Dimensions

Actual Depth	12.13 in
Actual Height	60.130 in
Actual Width	49.75 in
Depth	12 in
Height	60 in
Weight	485 lb

Width	50 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	12
UL Listed	Yes