



## WA726036FSDAD

by Wiegmann  
Catalog ID: WA726036FSDAD

N12 Two Door Dual Access Freestanding 72X60X36 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment. The addition of 19-inch rack mounting accessories make these enclosures ideal for providing rugged protection for sensitive rack mounted components in harsh industrial environments. The enclosures are found extensively in found in automotive, pulp and paper, wood products, textile, and similar industries. Style includes two door dual access (overlapping doors on front and rear).

## Product Details

### General

Application	Designed to protect electrical and electronic controls, components, and instruments in typical industrial environments. Enclosures protect enclosure equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3 Point Keylocking-Padlocking Combo
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725452804

### Dimensions

Actual Depth	36.25 in
Actual Height	72.120 in
Actual Width	60.12 in

Depth	36 in
Height	72 in
Weight	750 lb
Width	60 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes