



WA72X6112U

by Wiegmann
Catalog ID: WA72X6112U

N12 Two Door Floor-Mount Right Flanged Disconnect 72X61X12 Carbon Steel - Gray

Product Details

General

Application	The Wiegmann universal cutout is used in large freestand and floorstand enclosures.
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	15 in. floor stands
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725428601

Dimensions

Actual Depth	12.13 in
Actual Height	72.130 in
Actual Width	61.75 in

Depth	12 in
Height	72 in
Weight	630 lb
Width	62 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	12
UL Listed	Yes