



WA72X7324SSN4

by Wiegmann
Catalog ID: WA72X7324SSN4

N4X Two Door Floor-Mount Right Flanged Disconnect 72X73X24 304 Stainless Steel

Product Details

General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Method	15 in. floor stands
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725869688

Dimensions

Actual Depth	24.12 in
Actual Height	72.120 in

Actual Width	73.750 in
Cubic Capacity	127872 cu.in
Depth	24 in
Height	72 in
Weight	970 lb
Width	74 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes