



WB12S

by CMC
Catalog ID: WB12S

Ground Rod Clamps

- For direct burial
- For connecting ground wire to driven rod.
- Designed to maintain proper alignment between ground wire and rod
- Cast of high-strength copper alloy for corrosion resistance

Product Details

General

Hex Size	1/2 in
Material	Cast copper alloy
Type	Heavy-Duty Clamps

Dimensions

Rod Diameter	0.500 in
--------------	----------

Conductor Related

Conductor Range	2-10 AWG
-----------------	----------

Certifications and Compliance

Industry Standard(s)	UL/CSA certified
----------------------	------------------