



WC08C16

by Wiegmann
Catalog ID: WC08C16

N12 Operator Interface Console 8X16 Carbon Steel - Gray

Designed to house a variety of electronic control or instrumentation devices. Consoles provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either or two sides, creating control surfaces of 30 degrees or 60 degrees. Consoles can be mounted on desktops, pedestal or other flat surfaces.

- Fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Grounding provisions

Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Captive cover screws thread into sealed wells. Control panel is continuously hinged along bottom edge. Closed cell oil resistant neoprene gasket. Grounding provisions included.

Product Details

General

Application	Designed to house a variety of electronic control or instrumentation devices. Consoles provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either of two sides, creating control surfaces of 30 degrees or 60 degrees.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Series	WC-C
Type	Consoles

UPC	786725441105
-----	--------------

Dimensions

Actual Depth	7.09 in
Depth	7 in
Height	8 in
Weight	14 lb
Width	16 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes