



## WC1224T

by Wiegmann  
Catalog ID: WC1224T

Top For WC1224B Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on sloping control surfaces. Interior components can be mounted on standard back panel and terminal straps. Heavy duty construction provides protection from dirt, dust, oil and water.

- Fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Closed cell neoprene gasket is included

Fabricated from 14 gauge steel. Tops have a sloped front surface. Seams are continuously welded and ground smooth. Instrument and access panels have captive screws which thread into sealed well. 4 holes are provided in bottom of top for mounting to body. Closed cell neoprene gasket. Instrument panels and access panels are removable.

## Product Details

### General

Application	For use with WC1224B console.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Series	WC12
Type	Console Top

UPC	786725443345
-----	--------------

#### Dimensions

Actual Depth	20.13 in
Actual Height	6.120 in
Actual Width	24.13 in
Depth	20 in
Height	6 in
Weight	43 lb
Width	24 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes