

## WC1460BD


by Wiegmann

Catalog ID: WC1460BD

Prop65\_Cancer&Reproductive

N12 Double Door Console Body 50X60X23 Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels or relay rack angles (panels are optional). Heavy duty construction provides protection from dirt, dust, oil and water. Numerous accessories and variable combinations make these consoles most versatile.



\* Representative image

### Product Details

#### General

|                         |   |
|-------------------------|---|
| Application             | Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels, or relay rack |
| Color                   | Ansi-61 Gray Textured   |
| Construction            | Continuously Welded Seams   |
| Cover Type              | Door  |
| Finish Type             | Polyester Powder  |
| Latches Type            | 3-Point Keylocking Handle   |
| Listings                | UL, CSA   |
| Material                | Steel, Carbon   |
| Number of Doors (Fixed) | 2   |
| Series                  | WC14  |
| Type                    | Console Body  |
| UPC                     | 786725444601  |

#### Dimensions

|               |           |
|---------------|-----------|
| Actual Depth  | 23.13 in  |
| Actual Height | 50.130 in |
| Actual Width  | 60.13 in  |
| Depth         | 23 in     |

|        |        |
|--------|--------|
| Height | 50 in  |
| Weight | 311 lb |
| Width  | 60 in  |

#### Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | 12   |
| UL Listed        | Yes  |

#### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|