



WC20C20SS

by Wiegmann
Catalog ID: WC20C20SS

N12 Operator Interface Console 20X20 304 Stainless Steel

Designed to house a variety of electronic control or instrumentation devices. Consolets provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either or two sides, creating control surfaces of 30 degrees or 60 degrees. Consolets can be mounted on desktops, pedestals, or other flat surfaces.

- Fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Grounding provisions

Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth, less knockouts or holes. Captive cover screws thread into sealed wells. Control panel is continuously hinged along bottom edge. Closed cell oil resistant neoprene gasket. Grounding provisions included.

Product Details

General

Application	Designed to house a variety of electronic control or instrumentation devices. Consolets provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either of two sides, creating control surfaces of 30 degrees or 60 degrees.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Method	Grounding Provisions
Series	WC-SS
Type	Console
UPC	786725849543

Dimensions

Actual Depth	13.09 in
Depth	13 in
Height	20 in

Weight	36 lb
Width	20 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes