

Straight Blade Devices, Male Plug,
Insulgrip Heavy Duty,
Industrial/Commercial Grade,
Straight, 2-Pole 3- Wire Grounding,
20A 125V, 5-20P and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5366C](#)

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty,
Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding,
20A 125V, 5-20P, Black and White, Single Pack.

Features

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5366C
Color	Black, White
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	• Assembly Screws - Nickel plated steel • Blade Holder - Nylon



- Blades - .060 in. (1.5) Brass
- Housing/Cord Clamp - Nylon
- Terminal Clamp - Nickel plated steel
- Terminal Retainer - Clear Polycarbonate
- Terminal Screws - #8-32 Brass , multiple drive

Style	Standard
Type	Plug
UPC	783585173955

Dimensions

Dimensions	1.52 in x 1.52 in x 1.96 in
Height	1.96 in
Length	1.52 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
--------------------------	---

Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • Fed. Spec. W-C596G • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706	Catalog Page - WDK A-38 Catalog Page Catalogs - WDK Catalog Full 2024 Engineering Drawing - HBL5366C AutoCAD Drawing Installation Manuals - WIRING_PD2437_INSTALLINST Literature - PULP & PAPER SOLUTIONS Literature - Insulgrip® Straight Blade and Twist-Lock® Devices Literature - Pulp & Paper Solutions Literature - Wiring Device Solutions for Strategic Manufacturing Facilities Literature - Entertainment Product Solution Guide Literature - Industrial Solutions Literature - Emergency Preparedness for Healthcare Sales Drawings - WDK_HBL5366C_DRAWING_PDF Specifications - Wiring HBL5366C Specification Sheet Warranty - Industrial & Commercial Products Video - Insulgrip Twist-Lock and Straight Blade Devices
Nema Rating	5-20P	
Standards - RoHS Compliance Status	CM	
Logistics		
Carton Quantity	10	
Pallet Quantity	3600	
Product Assets		