

GFRST83W

Par Hubbell Wiring Device-Kellems
No de catalogue [GFRST83W](#)

Prise DDFT 20A de qualité hospitalière, Styleline, 125V, face
affleurante.



Caractéristiques

- Indicateur d'alimentation vert et indicateur de déclenchement rouge
- Technologie d'autotest brevetée AUTOGUARD®
- Construction à triple essuyage

Général

Catalog Number	GFRST83W
Couleur	<ul style="list-style-type: none">• White• Blanc
Indicateur EU RoHs	Contact Manufacturer
Série	Hospital Grade
Type	Standard
Type	Standard
UPC	783585485256

Caractéristiques électriques

Courant nominal	20 A
Description de la tension nominale	125 V

Certifications et conformité

Classe NEMA nominale	5-20R
Norme(s) de l'industrie	Meets All NEC® Requirements

Logistique

Quantité dans l'emballage	10
---------------------------	----

Documentation

- [Catalog Page - WDK L-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFRST83W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2082_INSTALLINST](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - Duct Products Guide](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - WDK_GFRST83_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)