

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
1-1/4 inch NPT, Straight Male Thread, Stainless Steel Mesh, Liquidtight	F5	1.000"-1.125" (2.54-2.86)	783585322087	07401027

## Listings

UL Listed  
CSA Certified

## Specifications

Strand	Stainless Steel
Body	Aluminum

## Performance


### Environmental

Flammability  
Hazardous Locations

UL 94HB (Strand grip), UL 94V-2(Fitting)  
Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures  
Wet Locations

-30°F to +240°F (-34°C to +115°C)  
Suitable for use in wet locations when used with a listed sealing ring between box and fitting



## Related Products

Locknut	00322004LPK50
Metal Clad Sealing O-Ring	20509004

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions