

### Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

### Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
90° Male Thread, Liquidtight, for Insulated Cables	F1	.375"-.437" (.95-1.11)	783585322544	07401073

### Listings


UL Listed  
CSA Certified

### Specifications

Strand	Stainless Steel
Body	Aluminum

### Performance

<b>Environmental</b>	
Flammability	UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations	Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Operating Temperatures	-30°F to +240°F (-34°C to +115°C)
Wet Locations	Suitable for use in wet locations when used with a listed sealing ring between box and fitting



### Related Products

Locknut	31622002LPK50
---------	---------------

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions