

Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Ordering Information

| Description | Form Size | Cable | UPC | Catalog Number |
|--|-----------|------------------------------|--------------|----------------|
| Straight Male Thread, F7 Stainless Steel Mesh, Liquidtight | | 1.937"-2.062" (4.92-5.24) | 783585322865 | 074011032 |




Listings

UL Listed
CSA Certified

Specifications

| | |
|--------|-----------------|
| Strand | Stainless Steel |
| Body | Aluminum |



Performance

Environmental

Flammability: UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations: Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C.

Operating Temperatures: -30°F to +240°F (-34°C to +115°C)
Wet Locations: Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

| | |
|---------------------------|----------|
| Metal Clad Sealing O-Ring | 20509007 |
|---------------------------|----------|

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions