

Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Ordering Information

| Description | Form Size | Cable | UPC | Catalog Number |
|--|-----------|------------------------------|--------------|------------------|
| 90° Male Thread, Liquidtight, for Insulated Cables | F5 | 1.125"-1.250" (2.86-3.17) | 783585322964 | 074011042 |

Listings


UL Listed
CSA Certified

Specifications

| | |
|--------|-----------------|
| Strand | Stainless Steel |
| Body | Aluminum |

Performance

| | |
|------------------------|---|
| Environmental | |
| Flammability | UL 94HB (Strand grip), UL 94V-2(Fitting) |
| Hazardous Locations | Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C |
| Operating Temperatures | -30°F to +240°F (-34°C to +115°C) |
| Wet Locations | Suitable for use in wet locations when used with a listed sealing ring between box and fitting |



Related Products

| | |
|---------------------------|---------------|
| Locknut | 00322004LPK50 |
| Metal Clad Sealing O-Ring | 20509004 |

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions