

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

| Description  | Form Size | Cable                     | UPC          | Catalog Number |
|--|-----------|---------------------------|--------------|----------------|
| 90° Male Thread, Liquidtight, for Insulated Cables | F5        | 1.000"-1.125" (2.54-2.86) | 783585322995 | 074011045      |

## Listings


UL Listed  
CSA Certified

## Specifications

|        |                 |
|--------|-----------------|
| Strand | Stainless Steel |
| Body   | Aluminum        |

## Performance

|                        |   |
|------------------------|---|
| Environmental          | UL 94HB (Strand grip), UL 94V-2(Fitting)  |
| Flammability           | Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C |
| Hazardous Locations    |   |
| Operating Temperatures | -30°F to +240°F (-34°C to +115°C)   |
| Wet Locations          | Suitable for use in wet locations when used with a listed sealing ring between box and fitting              |



## Related Products

|                           |               |
|---------------------------|---------------|
| Locknut                   | 00322005LPK50 |
| Metal Clad Sealing O-Ring | 20509005      |

## Online Resources

Customer Sales Drawings  
eCatalog