

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
90° Male Thread, Liquidtight, for Insulated Cables	F5	1.125"-1.250" (2.86-3.17)	783585323008	<b>074011046</b>

## Listings


UL Listed  
CSA Certified

## Specifications

Strand	Stainless Steel
Body	Aluminum

## Performance

<b>Environmental</b>	
Flammability	UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations	Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Operating Temperatures	-30°F to +240°F (-34°C to +115°C)
Wet Locations	Suitable for use in wet locations when used with a listed sealing ring between box and fitting



## Related Products

Locknut	00322005LPK50
Metal Clad Sealing O-Ring	20509005

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions