

Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Straight Male Thread, F8 Stainless Steel Mesh, Liquidtight		3.000"-3.250" (7.62-8.25)	783585330648	074011189




Listings

UL Listed
CSA Certified

Specifications

Strand	Stainless Steel
Body	Aluminum



Performance

Environmental

Flammability UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures -30°F to +240°F (-34°C to +115°C)
Wet Locations Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

Metal Clad Sealing O-Ring	20509008
---------------------------	----------

Online Resources

Customer Sales Drawings
eCatalog