

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

| Description  | Form Size | Cable                       | UPC          | Catalog Number |
|--|-----------|-----------------------------|--------------|----------------|
| 90° Male Thread, Liquidtight, for Insulated Cables | F5        | .750"- .875"<br>(1.90-2.22) | 783585341347 | 074011230      |




## Listings

UL Listed  
CSA Certified

## Specifications

|        |                 |
|--------|-----------------|
| Strand | Stainless Steel |
| Body   | Aluminum        |



## Performance

|                        |   |
|------------------------|---|
| <b>Environmental</b>   |   |
| Flammability           | UL 94HB (Strand grip), UL 94V-2(Fitting)  |
| Hazardous Locations    | Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C |
| Operating Temperatures | -30°F to +240°F (-34°C to +115°C)   |
| Wet Locations          | Suitable for use in wet locations when used with a listed sealing ring between box and fitting              |

## Related Products

|                           |               |
|---------------------------|---------------|
| Locknut                   | 00322004LPK50 |
| Metal Clad Sealing O-Ring | 20509004      |

## Online Resources

Customer Sales Drawings  
eCatalog