

Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Straight Male Thread, F6 Stainless Steel Mesh, Liquidtight		1.312"-1.437" (3.33-3.65)	783585497822	074011253




Listings

UL Listed
CSA Certified

Specifications

Strand	Stainless Steel
Body	Aluminum



Performance

Environmental

Flammability: UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations: Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures: -30°F to +240°F (-34°C to +115°C)
Wet Locations: Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

Locknut	00322005LPK50
Metal Clad Sealing O-Ring	20509005

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions