

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Straight Male Thread, F6 Stainless Steel Mesh, Liquidtight		1.687"-1.812" (4.28-4.60)	783585330846	<b>074011256</b>




## Listings

UL Listed  
CSA Certified

## Specifications

Strand	Stainless Steel
Body	Aluminum



## Performance

### Environmental

Flammability: UL 94HB (Strand grip), UL 94V-2(Fitting)  
Hazardous Locations: Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures: -30°F to +240°F (-34°C to +115°C)  
Wet Locations: Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## Related Products

Locknut	00322005LPK50
Metal Clad Sealing O-Ring	20509005

## Online Resources

Customer Sales Drawings  
eCatalog