

Features

- Aluminum fitting
- Stainless steel mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Straight Male Thread, F2 Liquidtight, for Insulated Cables		.187"-.250" (.47-.63)	783585498720	074011331




Listings

UL Listed
CSA Certified

Specifications

Strand	Stainless Steel
Body	Nylon



Performance

Environmental	
Flammability	UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations	Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Operating Temperatures	-40°F to +225°F (-40°C to +107°C)
Wet Locations	Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

Locknut	00322001LPK50
Metal Clad Sealing O-Ring	20509001

Online Resources

Customer Sales Drawings
eCatalog