

Features

- Aluminum Fitting
- Stainless steel mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Ordering Information

| Description | Form Size | Cable | UPC | Catalog Number |
|--|-----------|----------------------------|--------------|----------------|
| Straight Male Thread, F3 Liquidtight, for Insulated Cables | | .375"- .500" (.95-1.27) | 783585331065 | 074011335 |




Listings

UL Listed
CSA Certified

Specifications

| | |
|--------|-----------------|
| Strand | Stainless Steel |
| Body | Nylon |



Performance

| Environmental | |
|------------------------|---|
| Flammability | UL 94HB (Strand grip), UL 94V-2(Fitting) |
| Hazardous Locations | Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C |
| Operating Temperatures | -40°F to +225°F (-40°C to +107°C) |
| Wet Locations | Suitable for use in wet locations when used with a listed sealing ring between box and fitting |

Related Products

| | |
|---------------------------|---------------|
| Locknut | 00322002LPK50 |
| Metal Clad Sealing O-Ring | 20509002 |

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions