

Kellems® Wire Management Products
 PG and Metric Threaded Deluxe Cord Grips
 Deluxe Cord Grips

HUBBELL

Features

- Aluminum Fiting
- Stainless steel mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Ordering Information

Description	Hub Size	Cable	UPC	Catalog Number
Straight Panzergewinde Male Thread, Liquidtight	PG16	.500"-.625" (1.27-1.59)	783585327822	074PG16010

Listings

UL Listed
 CSA Certified

Specifications


Strand	Stainless Steel
Body	Aluminum

Performance

Environmental

Flammability UL 94HB (Strand grip), UL 94V-2 (Fitting)
 Hazardous Locations Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures -30°F to +240°F (-34°C to +115°C)
 Wet Locations Suitable for use in wet locations when used with a listed sealing ring between box and fitting



Related Products

Locknut LNP16BPK100

Online Resources

Customer Sales Drawings
 eCatalog
 Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

