

## Straight Blade Devices

### 15A, 125V, 2 Pole, 3 Wire Grounding

#### Hubbell-Pro™ Extra Heavy Duty Duplex Receptacles

# HUBBELL

#### Features

- Slender/compact design
- Smooth Face
- Triple wipe contacts

#### Ordering Information

Description	Device Color	UPC	Catalog Number
Back and side wired	Brown	783585530734	5252B

#### Listings

UL Listed to UL498 File No. E2186  
Certified to CSA 22.2, No. 42  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

#### Specifications

Material	Thermoplastic/Composite
Contacts	Brass
Mounting Strap	Galvanized steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

#### Performance

##### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

##### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminal wire leads identified in accordance with UL 498

##### Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



#### Accessories

Wallplate or Weatherproof Cover

Duplex Opening

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

