

Dimmers
1500W, 120V AC, 60Hz
Slide Control Dimmers

HUBBELL

Ordering Information

Description	Device Color	UPC	Catalog Number
Single pole/three way - preset	White	783585224053	AS153



Listings

UL Listed
CSA Certified

Online Resources

[eCatalog](#)

Specifications

Product Type	Dimmers
Dimmer Style	Architectural Grade Slider
Switch Type	Single Pole/Three Way

Performance

Environmental

Operating Temperatures Max Continuous -75°C, Minimum- -40°C Without Impact

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

