

Kellems® Wire Management Products
PolyTuff® II Non-Metallic Liquidtight Conduit
Liquidtight Tubing

HUBBELL

Features

- PVC core with corrugated walls bonded to PVC jacket
- Non-metallic construction ends metal fatigue and separation problems
- Handles twists, turns, bends, switchbacks and straightaways with ease



Ordering Information

Description	Device Color	UPC	Catalog Number
Non-Metallic, PolyTuff® II Tubing, Black	Black	78358533311	B2200

Listings

UL Recognized
CSA Certified

Online Resources

[eCatalog](#)

Specifications

Material	Co-extruded rigid and flexible PVC
Trade Size	2 Inch
Bend Radius Inches (mm)	5.00" (127.0)
Conduit ID/OD Inches (mm)	2.03"/2.36" (51.6/59.9)

Performance

Electrical

Voltage Rating 300V Maximum

Environmental

Operating Temperature 0°F to +140°F (-18°C to +60°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

