

Features

- Nylon Fitting
- Stainless steel mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Nylon Fittings and Mesh, Straight Male Thread	F3	.500"-.625" (1.27-1.59)	783585335063	CG610NM



Listings

UL Listed
CSA Certified

Specifications

Strand	Non-metal
Fittings	Nylon

Performance

Environmental	
Flammability	UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations	Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Operating Temperatures	-30°F to +225°F (-34°C to +107°C)
Wet Locations	Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

Locknut	31622007LPK50
Metal Clad Sealing O-Ring	20509002

Online Resources

eCatalog