

Features

- Nylon Fitting
- Stainless steel mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Stainless Steel Fittings and Mesh, Straight Male Thread	F3	.750"-.875" (1.90-2.22)	783585338163	CG614SST



Listings

UL Listed
CSA Certified

Specifications

Strand	Stainless Steel
Fittings	Stainless Steel

Performance

Environmental

Flammability	UL 94HB (Strand grip), UL 94V-2(Fitting)
Hazardous Locations	Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Operating Temperatures	-30°F to +240°F (-34°C to +115°C)
Wet Locations	Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Related Products

Locknut	31622007LPK50
Metal Clad Sealing O-Ring	20509002

Online Resources

eCatalog