

Load:Logic®  
Control Panels  
Dimming Switches

# HUBBELL

## Features

- Provide a variety of control options for up to 4 buttons in a single-gang configuration.
- Function specific button caps supplied with units
- Connect to dimming card using UTP RJ45 patchcords

## Complementary Products

Wallplate	NPS26W
Wallplate, Decorator Opening, Snap-on	NPS26W
Wallplate, Decorator Opening	NP26W
Wallplate, Decorator Opening, Stainless Steel	SS26

## Online Resources

eCatalog

## Ordering Information

Description	UPC Number	Catalog Number
Load Control Panel low voltage dimming switch, 3 button, WH	78358542838	CPSD3W

## Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

## Performance

### Electrical

Power Requirements Per switch: 10mA @ 30VDC Max

### Environmental

Operating Location Indoor Use Only  
Operating Temperature Operating temperature: 32° to 122°F (0° to 50°C)  
Relative humidity (non-condensing): 10% to 90%

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

