

Straight Blade Devices  
15A, 125V, 2 Pole, 3 Wire Grounding  
Commercial Specification Grade Style  
Line® Decorator Duplex Receptacles

# HUBBELL

## Features

- Fully insulated design with 8-inch stranded wire leads
- Tamper-resistant shutter complies with national electrical code requirements
- Aesthetic Style Line® decorator design
- Smooth face
- Triple wipe contacts

## Ordering Information

| Description   | Device Color | UPC          | Catalog Number |
|---|--------------|--------------|----------------|
| Leaded receptacles,<br>Decorator,<br>Tamper-Resistant | Gray         | 783585147444 | DR15GRYTRP2    |

## Listings

UL Listed to UL498 File No. E2186 File No. E2186  
Certified to CSA, C22.2, No. 42  
NEMA® WD-6 Compliant

## Specifications

|                                    |                                   |
|------------------------------------|-----------------------------------|
| Face                               | Nylon                             |
| Base                               | Nylon                             |
| Power Contacts                     | .030 in. (.8) Brass               |
| Ground Contact                     | .031 in. (.8) Brass               |
| Lead Wires                         | #12 AWG THHN stranded copper wire |
| Mounting Strap                     | .040 in. (1) Galvanized steel     |
| Automatic Self-grounding<br>Staple | Stainless steel                   |
| Mounting Screws                    | Galvanized steel                  |

## Performance

### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical

|                        |  |
|------------------------|--|
| Product Identification | Ratings are a permanent part of the device |
|------------------------|--|

### Environmental

|                        |   |
|------------------------|---|
| Flammability           | UL 94V-2  |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



## Accessories

Wallplate or Weatherproof Cover StyleLine® Decorator Opening

## Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

