

0-10V Dimmer
Combination Switch
Low Voltage Switches

HUBBELL

Features

- 4-button switch
- Bi-level lighting & partial ON operation
- Pilot Light
- Single Gang Design

Ordering Information

Description	UPC Number	Catalog Number
0-10V dimmer combo LV switch	783585565088	DSC010W

Listings

cULus

Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

Performance

Electrical

Current Sinking Capacity	50mA
Power Requirements	Per switch: 10mA @ 30VDC Max

Environmental

Operating Location	Indoor Use Only
Operating Temperature	32° to 122°F (0° to 50°C) Relative humidity (non-condensing): 10% to 90%



Complementary Products

Wallplate	NPS26W
Wallplate, Decorator Opening, Snap-on	NP26W
Wallplate, Decorator Opening	SS26
Wallplate, Decorator Opening, Stainless Steel	

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

