

**0-10V Dimmer**  
**Momentary Switch**  
**Low Voltage Switches**

# HUBBELL

## Features

- 3-button switch
- Vacancy Operation
- Pilot Light
- Single Gang Design

## Ordering Information

Description	UPC Number	Catalog Number
0-10V dimmer vacancy LV switch	783585564944	<b>DSM010W</b>



## Listings

cULus

## Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

## Performance

### Electrical

Current Sinking Capacity	50mA
Power Requirements	Per switch: 10mA @ 30VDC Max

### Environmental

Operating Location	Indoor Use Only
Operating Temperature	32° to 122°F (0° to 50°C) Relative humidity (non-condensing): 10% to 90%

## Complementary Products

Wallplate	NPS26W
Wallplate, Decorator Opening, Snap-on	NP26W
Wallplate, Decorator Opening	SS26
Wallplate, Decorator Opening, Stainless Steel	

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

