

Switches, Three Way  
15A, 120-277V AC

## HBL® Extra Heavy Duty Industrial Locking Switch

# HUBBELL

### Features

- Large brass binding head screws with deep slots
- Lock circuits On or Off
- Strip gauge for accurate wiring

### Ordering Information

| Description                    | Color | UPC          | Catalog Number |
|--------------------------------|-------|--------------|----------------|
| Key Guide, back and side wired | Ivory | 783585188508 | HBL1203LI      |

### Listings

UL Listed  
CSA Certified  
Fed. Spec. W-S-896

### Specifications

|                 |                 |
|-----------------|-----------------|
| Top Material    | Thermoset       |
| Base Material   | Thermoset, Blue |
| Toggle Material | Metallic, Ivory |
| Contacts        | Silver Alloy    |
| Terminal Screws | Brass           |
| Ground Screw    | Brass (Green)   |

### Performance

#### Electrical


|                         |  |
|-------------------------|--|
| Dielectric Voltage      | Withstands 1500V AC minimum for 1 minute       |
| Max. Continuous Current | 15A  |
| Max. Working Voltage    | 277V AC  |
| Overload                | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise        | 30°C maximum at rated current                  |

#### Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper wire only

#### Environmental

|                       |  |
|-----------------------|--|
| Flammability          | UL 94V-2   |
| Operating Temperature | Max. continuous: 75°C; Min. continuous: -40°C without impact |



### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

