

Temporary Power
Temporary Industrial Lighting
A Type Twist-Lock® and Straight Blade
Light Strings

HUBBELL

Ordering Information

Description	UPC	Catalog Number
Straight Blade light string; plastic guards	783585528229	HBL123S50PS

Listings

UL
CSA
ETL

Specifications

Plug Type	NEMA 5-15P
Weight	14 lbs
Guard Material	Pre-A.* Plastic

Performance

Electrical

Max Watts per Fixture	150
Rating	15A 125V

Mechanical

Cord Length	50 ft.
Cord Type	12/3 STW
Number of fixtures	5



Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

