

Temporary Power  
Temporary Industrial Lighting  
A Type Twist-Lock® and Straight Blade  
Light Strings

# HUBBELL

## Ordering Information

Description	UPC	Catalog Number
Straight Blade light string; plastic guards	783585528243	HBL123SJ100PS

## Listings

UL  
CSA  
ETL

## Specifications

Plug Type	NEMA 5-15P
Weight	18 lbs
Guard Material	Pre-A.* Plastic

## Performance

### Electrical

Max Watts per Fixture	150
Rating	15A 125V

### Mechanical

Cord Length	100 ft.
Cord Type	12/3 STJW
Number of fixtures	10



## Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

