

Single Pole Devices and Temporary Power

Series 18 - 400A, 600V AC/DC

Female Plug

Features

- Extra Long non-conductive inner sleeve
- Turn and Lock Symbol aids in the mating of devices
- Easily Identifiable Cable with cut off points for secure fit

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|---|--------------|-------------|----------------|
| 400A, thermoplastic elastomer, cable size 3/0 - 4/0 AWG | White | 78358553952 | HBL18400FW |

Listings

UL and cUL Listed
UL Enclosure Types 3R, 4X, 12
National Electric Code (NEC), ANSI/NFPA 70

Specifications

| | |
|--------------------------|-------------------------|
| Base Compound | Thermoplastic Elastomer |
| Contact Material | Brass |
| Retaining Screw Material | Nylon |

Performance

Electrical

| | |
|-----------------|--------------------|
| Amperage Rating | 400A Maximum |
| Voltage Rating | 600V AC/DC Maximum |



Mechanical

| | |
|------------------------|--|
| Product Identification | Ratings are a permanent part of device |
| Terminal Accommodation | 3/0 to 4/0 AWG |

Environmental

| | |
|--------------|-------------------------------|
| Flammability | HB per UL94 or CSA 22.2. 0.17 |
|--------------|-------------------------------|

HUBBELL



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

