

Twist-Lock® Devices
 20A, 125V AC, 2 Pole, 3 Wire Grounding
 Valise® Plug

HUBBELL

Features

- One piece body design uses less fasteners for ease of assembly
- Powerful cord grip prevents conductor slippage and strain on wiring terminals
- Totally insulated impact and crush resistant nylon body
- Unique patented clamp type terminals provide a superior electrical connection by bundling the conductor strands when clamps are tightened

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Yellow nylon.	.325"-.720" (8.26-18.3)	783585235530	HBL2311VY

Listings

Listed to UL 498
 Fed.Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications

Housing	Yellow nylon
Blades	Brass
Terminal Screws	#8 - 32 Steel (Philips / Slotted / Robertson)
Terminal Clamps	Steel - Nickel plated
Clamp Screws	#8 - 32 Steel - Zinc plated (Philips / Slotted / Robertson)

Performance

Electrical


Current Interrupting	Certified for full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Terminal Accommodation	#18 AWG - #10 AWG stranded copper wire only.
------------------------	--

Environmental

Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C Minimum -40°C (w/o impact)
Terminal Identification	Terminals identified in accordance with UL 498



Accessories

Connector	HBL2313VY
Single Receptacle	HBL2310
Flanged Receptacle	HBL2316
Weatherproof Boot	HBL60CM31V

Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

