

Twist-Lock® Devices  
 20A, 3 Phase 480V AC; 3 Pole, 4 Wire  
 Grounding  
 Corrosion Resistant Insulgrip® Connector

# HUBBELL

## Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

## Ordering Information

| Description                        | Cord Diameter       | UPC          | Catalog Number |
|------------------------------------|---------------------|--------------|----------------|
| Corrosion resistant, yellow nylon. | .350"-1.150" (9-29) | 783585038520 | HBL24CM33      |

## Listings

Listed to UL 498  
 Fed.Spec. W-C-596  
 Certified to CSA C22.2 No.42

## Specifications

|                      |  |
|----------------------|--|
| Housing / Cord Clamp | Nylon  |
| Terminal Retainer    | Clear polycarbonate                            |
| Contacts             | Nickel Plated Brass                            |
| Terminal Screws      | #10-32 Bronze (Phillips / Slotted / Robertson) |
| Terminal Clamp       | Cold rolled steel – nickel plated              |
| Assembly Screws      | Steel - nickel plated                          |

## Performance

### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical


|                         |  |
|-------------------------|--|
| Terminal Accommodation  | #16 AWG - #8 AWG stranded copper wire only.    |
| Terminal Identification | Terminals identified in accordance with UL 498 |

### Environmental

|                        |  |
|------------------------|--|
| Flammability           | HB or better per UL94 or CSA 22.2 No. 0.6          |
| Moisture Resistance    | IP20 Suitability                                   |
| Operating Temperatures | Maximum Continuous 75°C Minimum -40°C (w/o impact) |



20A 3Ø 480V AC  
 NEMA L16-20R  
 UL/CSA  
 5 HP



## Accessories

|                   |           |
|-------------------|-----------|
| Plug              | HBL24CM31 |
| Weatherproof Boot | HBL60CM36 |

## Resources

Customer Use Drawing  
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

