

**Features**

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

**Ordering Information**

| Description               | Device Color | UPC Number  | Catalog Number |
|---------------------------|--------------|-------------|----------------|
| Nylon casing, back wired. | White        | 78358568165 | HBL2515ST      |

**Listings**

Listed to UL 498  
 Fed.Spec. W-C-596  
 Certified to CSA C22.2 No.42

**Specifications**

|                       |                                   |
|-----------------------|-----------------------------------|
| Housing               | Nylon                             |
| Terminal Retainer     | Nylon                             |
| Plunger               | Nylon                             |
| Blades                | Copper Alloy                      |
| Terminal Spring Clamp | Spring Steel                      |
| Assembly Screws       | Zinc Plated Tri-drive             |
| Mounting Screw        | Nickel Plated Brass, 8- 32 Thread |
| Weight (lbs)          | 0.3                               |

**Performance****Electrical**

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 3,000V minimum                                |

**Mechanical**

|                         |   |
|-------------------------|---|
| Terminal Accommodation  | #14 AWG - #6 AWG solid or #14AWG - #8AWG stranded copper wire |
| Terminal Identification | Terminals identified in accordance with UL 498                |

**Environmental**

|                        |   |
|------------------------|---|
| Flammability           | HB or better per UL94/CSA 22.2 No.0.17              |
| Moisture Resistance    | IP20 Suitability                                    |
| Operating Temperatures | Maximum Continuous 75°C, Minimum -40°C (w/o impact) |

**Online Resources**

Customer Sales Drawings  
 eCatalog  
 Installation Instructions