

Twist-Lock® Devices
 30A, 125V AC, 2 Pole, 3 Wire Grounding
 Valise® Connector

HUBBELL

Features

- Powerful cord grips prevent conductor slippage and strain on wiring terminals
- Totally insulated impact and crush resistant nylon body



30A 125V
 NEMA L5-30R
 UL/CSA
 2 HP



Ordering Information


Description	Cord Diameter	UPC	Catalog Number
Yellow nylon.	.590"-.930" (15.0-23.6)	783585235981	HBL2613VY

Listings

Listed to UL 498
 Fed.Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications

Housing	Yellow nylon
Contacts	Brass
Terminal Screws	#8 - 32 Steel (Philips / Slotted / Robertson)
Terminal Clamps	Steel - Nickel plated
Clamp Screws	#8 - 32 Steel - Zinc plated (Philips / Slotted / Robertson)



Performance

Electrical	
Current Interrupting	Certified for full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#14 AWG- #8 AWG stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Moisture Resistance	IP20 Suitability
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)

Accessories

Plug	HBL2613VY
Plug	HBL2611VY
Flanged Inlet	HBL2616
Weatherproof Boot	HBL60CM32V

Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

