

Non-NEMA Twist-Lock® Devices  
 20A, 3 Phase Y 120/208V AC- only, 400 Hz, 4  
 Pole, 5 Wire Grounding  
 Variload® Flanged Inlet

# HUBBELL

## Features

•

## Ordering Information

Description	Device Color	UPC	Catalog Number
4P5W, 20A 3PH 120/208V AC Max, Non-NEMA, White Nylon	Black	783585238203	HBL45985CL

## Listings

Listed to UL 498

## Specifications

Flanged Housing	Nylon
Terminal Clamp	Cold rolled steel-nickel-plated
Blade Holder	Molded thermoset
Blades	Brass
Terminal Screw	Brass

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 2,000V minimum



### Mechanical

Terminal Accommodation	#14 AWG - #10 AWG solid or stranded copper wire only.
------------------------	---

Terminal Identification	Terminals identified in accordance with UL 498
-------------------------	--

### Environmental

Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



## Accessories

Connector	HBL45935
Weatherproof Lift Cover	WP2

## Resources

Customer Use Drawing  
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

