

Hospital Products

Power Strips

Healthcare Facility Outlet Assemblies

HUBBELL

Features

- Industry first offering of UL Listed power strips that are for use in Patient Care Areas
- Approved by CMS (Center for Medicaid and Medicare Services) for use in all types of health care facilities
- Tamper resistant covers



Ordering Information

| Description | Color | Catalog No. | UPC |
|---|-------|-------------|--------------|
| Surge Protective Devices, 15A, HCOA 4 Outlet Strip, 6' Cord | White | HBL4MG6 | 783585588230 |

Listings

UL2930 Listed

Specifications

Physical

| | |
|-------------|-----------------------|
| Cord | 12/3 SJT |
| Housing | 18G Galvanized Steel |
| Color | White Powder Coat |
| Receptacles | HG Tamper Resistant |
| Plug | Straight Plug |
| LED | Green Power Indicator |

Electrical

| | |
|-----------------|------|
| Current | 15A |
| Voltage | 125V |
| Frequency | 60Hz |
| Surge Component | MOV |

Dimensions

| | |
|--------|------------------|
| Length | 11.90" (302.3mm) |
| Width | 2.22" (56.4mm) |
| Depth | 1.92" (48.7mm) |

Environmental

| | |
|-----------------------|--------------------------------|
| Operating Temperature | -40°F to 160°F (-40°C to 70°C) |
|-----------------------|--------------------------------|

Performance

| | |
|---|---|
| UL VPR | L-N 600V L-G, N-G n/a |
| EMI Noise Filtration In (Nominal Discharge Current) | -11 dB to -68 dB (10kHz to 100MHZ) 3kA |
| MCOV | 150V |
| Peak Current Rating L-N | 30kA |
| Leakage Current | <.1mA |
| Total Joules (L-N) | 550j |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031
Specifications subject to change without notice.



Wiring Device-Kellems