

# Hospital Products

## Power Strips

### Healthcare Facility Outlet Assemblies

# HUBBELL

#### Features

- Industry first offering of UL Listed power strips that are for use in Patient Care Areas
- Approved by CMS (Center for Medicaid and Medicare Services) for use in all types of health care facilities
- Tamper resistant covers



#### Ordering Information

Description	Color	Catalog No.	UPC
Relocatable Power Tap, 20A, HCOA 4 Outlet Strip, 15' Cord	White	HBL4MGRPT1520	783585588308

#### Listings

UL2930 Listed

#### Specifications

##### Physical

Cord	12/3 SJT
Housing	18G Galvanized Steel
Color	White Powder Coat
Receptacles	HG Tamper Resistant
Plug	HG 45° Angle
LED	Green Power Indicator

##### Electrical

Current	20A
Voltage	125V
Frequency	60Hz
Surge Component	MOV

##### Dimensions

Length	9.15" (232.4mm)
Width	2.22" (56.4mm)
Depth	1.92" (48.7mm)

##### Environmental

Operating Temperature	-40°F to 160°F (-40°C to 70°C)
-----------------------	--------------------------------

#### Performance

UL VPR	L-N 600V L-G, N-G n/a
EMI Noise Filtration In (Nominal Discharge Current)	-11 dB to -68 dB (10kHz to 100MHZ) 3kA
MCOV	150V
Peak Current Rating L-N	30kA
Leakage Current	<.1mA
Total Joules (L-N)	550j

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031  
Specifications subject to change without notice.



Wiring Device-Kellems