

Hospital Products

Power Strips

Healthcare Facility Outlet Assemblies

HUBBELL

Features

- Industry first offering of UL Listed power strips that are for use in Patient Care Areas
- Approved by CMS (Center for Medicaid and Medicare Services) for use in all types of health care facilities
- Tamper resistant covers



Ordering Information

Description	Color	Catalog No.	UPC
Relocatable Power Tap, 15A, HCOA 4 Outlet Strip, 15' Cord	White	HBL4MGRPT15	783585588285

Listings

UL2930 Listed

Specifications

Physical

Cord	12/3 SJT
Housing	18G Galvanized Steel
Color	White Powder Coat
Receptacles	HG Tamper Resistant
Plug	Straight Plug
LED	Green Power Indicator

Electrical

Current	15A
Voltage	125V
Frequency	60Hz
Surge Component	MOV

Dimensions

Length	9.15" (232.4mm)
Width	2.22" (56.4mm)
Depth	1.92" (48.7mm)

Environmental

Operating Temperature	-40°F to 160°F (-40°C to 70°C)
-----------------------	--------------------------------

Performance

UL VPR	L-N 600V L-G, N-G n/a
EMI Noise Filtration In (Nominal Discharge Current)	-11 dB to -68 dB (10kHz to 100MHZ) 3kA
MCOV	150V
Peak Current Rating L-N	30kA
Leakage Current	<.1mA
Total Joules (L-N)	550j

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031
Specifications subject to change without notice.



Wiring Device-Kellems