

Straight Blade Devices
15A, 125V, 2 Pole, 3 Wire Grounding
Heavy Duty, Single Receptacle

HUBBELL

Features

- Slender/compact design
- Triple wipe contacts
- Panel mount

Ordering Information

Description	Device Color	UPC	Catalog Number
Panel mount 1.75 in. (44.5) centers.	Ivory	783585014623	HBL5258I

Listings

UL Listed, File E2186
Certified to CSA, C22.2, No. 42
Fed. Spec. WC596
NEMA® WD-6 Compliant

Specifications

Body	PBT
Insulator	RTP
Contacts	Brass
Terminal Screws	Brass
Mounting Strap	Galvanized steel
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Galvanized Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 V-0
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

