

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Heavy Duty, Specification Grade Tamper-Resistant Duplex Receptacles

HUBBELL

Features

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Brass mounting strap and Triple Wipe contacts
- High impact resistant face with circuit I.D. marking area
- Complies with National Electrical Code (NEC®) requirements for Tamper Resistant receptacles

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Fed-Spec listed, Smooth nylon face, back and side wired, duplex	Blue	783585542409	HBL5262BLTR

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	PBT
Power Contacts	Brass
Ground Contact	Brass
Clamping Plate	Plated steel
Mounting Strap	Brass
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

Performance

Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#12-10 AWG stranded or solid copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

